



INSPIRSTAR INC. IS02 Microcurrent Stimulator

The First FDA-Approved Programmable Microcurrent Stimulation Machine

Product Advantages

- ★ A unique, flexible, digitally-programmable solution to microcurrent practitioners
- ★ Programmable with your own treatment protocols
- ★ Deployable for your own specific combinations of currents, frequencies and therapy time.
- ★ Easy and precise control for therapy making it ideal for routine treatment at both office and home.
- ★ Simple operation: select a protocol, and press START

Key Features

- ★ Five programmable protocols
- ★ Each protocol with a sequence of frequency pairs according to your own need.
- ★ Programmable frequency, current intensity, timer
- ★ Programmable advanced parameters for polarity, wave slopes and duty cycles
- ★ Two independent output channels
- ★ Easy programming with Windows based software
- ★ Storage memory for about 100 total Paired Frequencies*
- ★ Use of two 1.5V AA batteries for up to 80 hours of continuous running*

What Do Doctors Say?

"IS02 provides our customers with a unique, flexible, digitally-programmable machine for home use. IS02 can be programmed with your own treatment protocols and it can be re-programmed repeatedly. It helps microcurrent stimulation practitioners to choose specific combinations of currents and frequencies..." - Dr. Edward Kondrot

"The FSM Programmable Unit has been a welcome addition to my clinic. These convenient, portable, and programmable units allow my patients an affordable therapeutic option for more than one health concern at a time. The software is surprisingly easy to use and the customer support is terrific. I really like the ease in which I can customize FSM treatment protocols for each patient, and know that compliance will be high as they can treat themselves at home." - Dr. Anne Marie Fine
More testimonials on our website www.inspirstar.com.

Please find enclosed order form. Visit our website www.inspirstar.com for more information.

* Numbers vary with programmed protocols.

Inspirstar Inc. www.inspirstar.com
1259 E. Bautista Rd. Gilbert, AZ 85296
Phone: 480-634-8708, 1-866-643-0180
Fax: 480-634-8982 sales@inspirstar.com

Rev 1.0, © 2006 Inspirstar Inc.



Key Technical Specifications

- ★ Frequency Range: 0.1Hz ~ 999.9Hz
- ★ Frequency Accuracy: better than $\pm 0.5\%$
- ★ Current Intensity: 20 μ A ~ 400 μ A in 10 μ A steps
- ★ Timer: 0~60 minutes for each frequency
- ★ Wave Period: 4ms ~ 60s
- ★ Wave slope: fully programmable
- ★ Batteries: 2xAA 1.5V Alkaline
- ★ Storage Memory: typically 60 ~ 100 frequency pairs, up to 140 freq. pairs
- ★ Output Connector: 2 x 3.5mm mono jack